
All technical data presented represent typical results, unless stated otherwise as min/max values. No guarantee is made that material will meet exactly the values shown.

## Heat Sealer for Fourth Side of Pouch with Vacuum Electrolyte Filling





The design and its dimensions are subject to change for further improvements.

## **Specifications**

Objective: To heat seal a laminated puch cell by impulse-sealer after filling electrolyte under vacuum. Three

sides of the cell must be closed prior to this operation.

Sealing Method: Heat-bars

Min. Pressure: -90KPa, by Vacuum pump, monitored.

Electrolyte: Dispensed by tubing dispenser: T710 (no volume limit)

The electrolyte volume is controlled by # of rotations of the dispenser.

Cell size: 100mm x 100mm ~ 297mm x 210mm

Seal Width: 5 ~ 10mm

Temperature: ~ 300°C

Air (Ar.) supply: 0.5MPa, Terminal with PT1/4

Size: 680mmW x 400mmD x 800mmH

Weight: 80kg [HSTS-06], 19kg [vacuum pump]

Power: AC100V, 50/60 Hz, 15A

Flow-chart:

Vacuum > e-filling nozzle down > e-filling > e-filling nozzle up > heat-sealing > releasingto atmospheric pressure

\*Time and the sequence are controlled digitally on the touch panel.

**Application:** Advanced energy

Product type: Machinery

Production scale: Lab, Pilot

Search tags: Hohsen, Machinery, Pouch sealer, Electrolyte filler